# **BrightWater Environmental Titanium AOP Water Purification**





# **Titanium Advanced Oxidation Process**


Chemical free destruction of all contaminates, microbiological matter and organic compounds

The Advanced Oxidation Process (AOP) offers unique new levels of performance for purification of drinking water supplies. It is chemical free and utilises "a non-selective" destruction mechanism that destroys all contaminates and microbiological matter present in the water.

The non-selective "destroy-all" technology gives complete oxidation and purification of the water system and represents a watershed in the advancement of water treatment technology. The Titanium AOP will break down and de-decompose any organic matter present in the water to leave a truly purified water. Everything organic is decomposed back to H2O, CO2 and O2.

#### Titanium AOP - Features & benefits

- Ensures the non-selective destruction of all organic Photocatalytic Oxidation and Hydroxyl Radicals matter quickly and easily
- Environmentally friendly
- Cost effective as expensive chemicals are not required
- · Eliminates risk of over dosing with chemicals and subsequent corrosion to pipework and valves
- Photocatalytic Oxidation and Hydroxyl Radicals
- have the highest Oxidation strength for the destruction of waterborne contminates of any
- decompose organic and microbiological matter, contaminates, pollutants, hydrocarbons and help prevent biofilms forming
- Low energy consumption
- Simple, low cost maintenance procedures
- Proven track record installed worldwide



### The Chemistry at work

The Advanced Oxidation Process uses a Titanium vessel with a patented titanium dioxide crystal coating on the internal surface. This surface reacts with UV light at 254nm to produce two very powerful Oxidation reactions – Photocatalytic Oxidation and Hydroxyl Radical Oxidation. The rate of destruction for organic contaminates utilizing these two reactions is higher than all other commercially available oxidation systems.

To demonstrate the effectiveness of the two reactions Photocatalytic Oxidation and Hydroxyl Radical Oxidation we have set out in the table below the simple performance comparison of the various oxidation methods.

Oxidant	Formula	
Photocatalytic Oxidation	TiO2 + (UV at 254nm)	3.21
Fluorine	F2	2.87
Hydroxyl Radical	OH•	2.8
Single Oxygen	O (1D)	2.42
Ozone	O <sub>3</sub>	2.07
Hydrogen Peroxide	H <sub>2</sub> O <sub>2</sub>	1.78
Permanganate	MNO <sub>4</sub>	1.67
Hypochlorous Acid	HCOI	1.48
Monochloromine	NH <sub>2</sub> CI	1.4
Chlorine	Cl <sub>2</sub>	1.36
Hypobromus Acid	HOBr	1.33
Oxygen	O <sub>2</sub>	1.23
Bromide	Br <sub>2</sub>	1.07
Chlorine Dioxide	CIO <sub>2</sub>	0.95

The Titanium AOP System works by a physical process. It exploits the effect of UV light at 254nm upon a Titanium Dioxide surface in the presence of

dioxide

water. The resultant Hydroxyl Radicals are highly reactive, attacking and eradicating any organic contaminates and pollutants present.

The high energy UV photons generated in the rector drive two major processes:


The first process is a Photocatalytic Oxidation reaction that occurs at the reactor surface when UV light at 254nm hits the Titanium Dioxide surface. This reaction will immediately oxidise any organic matter at the surface of the reactor with an Oxidation Strength of 3.21(eV) this is the strongest possible Oxidation strength possible in a potable water supply. This happens by the UV light promoting electrons at the reactor surface to a higher energy level creating an electron / hole (TiO<sub>2</sub>e-h+) pair. Most promoted electrons will return to their lower energy level state by emitting light.

The second reaction caused by the Titanium Dioxide and UV light at 254nm is reaction of generating Hydroxyl Radicals (OH). The Hydroxyl Radical OH will also oxidise any organic contaminates present by removing the Hydrogen atom. If no organic matter exists the Hydroxyl Radical will recover hydrogen to reform into water.

The Titanium AOP system does not affect pH, proving that all Hydrogen atoms are converted back to water within the chamber.

The Hydroxyl Radical has an Oxidation Strength of 2.87(eV).


By the action of water flow passing through the reactor (an oxidation hot zone) the whole liquid volume has all organic and microbiological matter destroyed and decomposed. Due to their extreme reactivity Hydroxyl Radicals only exist for a matter of milliseconds before reverting back to water. As a result all reactions only take place within the titanium reactor.



dioxide

#### **Specifying Titanium AOP**

- The water purification unit shall break down and destroy all waterborne organic matter, to include fungi, yeast, amoebae and viruses by the use of Hydroxyl Radicals.
- . The purification process will take place by means of an Advanced Oxidation Process.
- Hydroxyl Radicals to be created by photonic energy at wave-length of 254nm combined with the photo-catalysis Titanium Dioxide.
- . The body of the unit shall be of Titanium Dioxide construction with a Titanium Dioxide Crystal coating applied to the internal surfaces of the reactor body to maximise the photo-catalytic reaction creating Hydroxyl Radicals.
- The Hydroxyl Radicals will have a Redox Potential of The controls should include facilities for a UV 2.8 to ensure complete oxidation of waterborne contaminates.
- . No additives shall be used in the process and no harmful residuals shall be formed.
- . The unit shall include a full controls system that runs form a 230V 50Hz fused spur supply.



- intensity monitor and remote BMS alarm.
- Water purification system shall be Titanium AOP from Brightwater Environmental Ltd or equal and approved subject to a technical submittal demonstrating compliance with the above criteria.

Model	AOP 5	AOP 10	AOP 20	AOP 50	AOP 100
Throughput					
Maximum flow (L/sec)	1.40	2.80	5.5	13.9	27.7
Maximum flow (m3/hr)	5	10	20	50	100
Water pressure drop (bar)	<0.1	<0.1	<0.1	<0.1	<0.1
Electrical specifications					
Voltage (V)	230	230	230	230	230
Power consumption (W)	100	200	380	700	1300
Fuse rating (A)	3	3	3	5	13
Number of lamps	1	2	4	8	14
Reactor					
Diameter x length (mm	110x790	155x790	220x800	270x800	340x800
Material	Titanium	Titanium	Titanium	Titanium	Titanium
Connections	11/2" BSP male	2" BSP male	DN100 Flange	DN125 Flange	DN150 Flang
Controls Cabinet Dimensions (mm)	260 x 190 x 80	400 x 300 x 250	500 x 500 x 250	600 x 600 x 250	800 x 800 x 300
Weight (kg)	20	26	28	30	48

## **BrightWater Environmental**

Grove Barn, Middle Road, Denton, Harleston, Norfolk IP20 0AH T 020 3303 3249 E sales@brightwaterenvironmental.co.uk W www.brightwaterenvironmental.co.uk

